

Basic Type Code Information

| | | | | |
|-------------------------------|--|--------------------------|---|---|
| ACS800 Product Series | -U1 Construction U1 = Wall Mounted U2 = Floor Standing Drive U7 = Cabinet Drive 07 = Cabinet Drive (Multi-module) 17 = Cabinet Drive (Regenerative) | -0025 KVA Rating | -5 Voltage 2 = 208, 220, 230, 240Vac 3 = 380, 400, 415Vac 5 = 380, 400, 415, 440, 460, 480, 500Vac 7 = 525, 550, 575, 600, 690Vac | +L500 Options See Options List |
|-------------------------------|--|--------------------------|---|---|

Ordering Information

To order an ACS800 drive, select the appropriate type code from the following pages for your input voltage, motor current, and drive construction desired. This then represents the basic drive product. To add options, simply add a [+] to the end of the type code followed by the plus code of the desired option.

Adding a number in front of the option indicates the quantity of that option for the drive. A zero is used to delete a standard option. E.g. 2L501 means two (2) RDIO-01 modules, a 0C111 means to delete the extended enclosure from the standard U2 type floor standing drive.

Example: ACS800-U1-0030-5+D150+L501+K462 means add Brake Chopper, RDIO-01, and ControlNet fieldbus
+D150 = Brake Chopper, +L501 = RDIO-01, +K462 = ControlNet fieldbus

NOTE: When adding Plus Codes to an order, please provide them in Alphanumeric order.